



GRUNDIG

R

97 WE I
97 WE II
97 BE I

Repair Manual

IF-Alignment 460 kc

Wave Range, Variable Capacitor setting	Coupling of Signal Generator	Alignment	Sensitivity	Remarks
SW , turned in	G1 EF 89-G1 DF 91	I and II maximum	WE I 700 μ V WE II 700 μ V BE I 3 mV	During alignment damp alternately with $3nF + 10k\Omega$ in series. IF-Bandwidth: WE I/BE I 4.5 kc WE II 4.3 kc IF-Selectivity: WE I 1:140 WE II 1:130 BE I 1:70
	G1 ECH 81-G3 DK 92	III and IV maximum	WE I 12 μ V WE II 12 μ V BE I 80 μ V	
MW , turned in	to aerial	V minimum		Locking } WE I/WE II 1:30 depth } BE I 1:20
1 Mc	G1 ECH 81-G3 DK 92		WE I 15 μ V WE II 12-22 μ V BE I 90 μ V	Mixing sensitivity

Oscillator and Input Circuit Alignment (dummy aerial to aerial and ground sockets)

Wave Range, Frequency, Pointer setting	Oscillator	Input Circuit	Oscillating Current μ A	Sensitivity μ V	Image Suppression	Remarks			
97 WE I/97 BE I									
SW II	11 Mc	1 maximum	inner 2 maximum	WE I 230-380-200 BE I 120-200	24-18	1:6-1:4			
	21 Mc		4 maximum		240-120	1:4-1:3.5			
SW I	3.7 Mc	3 maximum	inner 6 maximum	WE I 230-330-260 BE I 140-230	40-45	1:8-1:8			
	8.5 Mc		8 maximum		10-11	1:25-1:10			
MW	560 kc	5 maximum	inner 10 maximum	WE I 280-420 BE I 160-170	6-6.5	1:240-1:100			
	1450 kc	7 maximum	12 maximum		27-35	1:250-1:100			
97 WE II									
SW II	11 Mc	1 maximum	2 maximum	230-380-200	22-23	1:11-1:5			
	21 Mc		4 maximum						
SW I	3.7 Mc	3 maximum	inner 6 maximum	230-330-260	8-11	1:44-1:32			
	8.5 Mc		8 maximum						
MW	560 kc	5 maximum	inner 10 maximum	280-420	6-9	1:480-1:360			
	1450 kc	7 maximum	12 maximum						
LW	160 kc	9 maximum	14 maximum	260-380-360	7-8	1:850-1:350			
	350 kc	11 maximum							
Volume control opened $f_i < f_o$									
The aligning is to be done in such sequen- ce that the aligning frequencies appear at the given positi- ons on the dial scale.									
Repeat aligning a few times and end with trimmer.									

Hum: WE I: control closed 2 mV; control opened 3 mV. WE II: control closed 1.7 mV; control opened 3 mV.

BOTTOM VIEW OF CHASSIS FOR MODEL 97 BE I



